



# TDS Water Quality Sensor

(Model: MW-TDS101)

## Manual

Version: 1.0

Valid Date: 2021-11-26

郑州炜盛电子科技有限公司  
Zhengzhou Winsen Electronic Technology Co., Ltd

# Statement

This manual copyright belongs to Zhengzhou Winsen Electronics Technology Co., LTD. Without the written permission, any part of this manual shall not be copied, translated, stored in database or retrieval system, also can't spread through electronic, copying, record ways.

Thanks for purchasing our product. In order to let customers use it better and reduce the faults caused by misuse, please read the manual carefully and operate it correctly in accordance with the instructions. If users disobey the terms or remove, disassemble, change the components inside of the sensor, we shall not be responsible for the loss.

The specific such as color, appearance, sizes &etc, please in kind prevail.

We are devoting ourselves to products development and technical innovation, so we reserve the right to improve the products without notice. Please confirm it is the valid version before using this manual. At the same time, users' comments on optimized using way are welcome.

Please keep the manual properly, in order to get help if you have questions during the usage in the future.

Zhengzhou Winsen Electronics Technology CO., LT

## MW-TDS101 TDS Water Quality Sensor

### Profile

MW-TDS101 is an online water quality detection sensor that can be used to detect the content of total dissolved solids (TDS) in water to judge the cleanliness or pollution of water.

The unit of measurement for TDS is mg/L, which indicates how many mg of dissolved solids are dissolved in 1L of water. The higher the TDS value, the more dissolved solids the water contains.



Figure 1: TDS sensor

### Sensor characteristics

High precision, fast response, good stability, small size and easy installation.

### Main Application

It is widely used in laboratory scientific research, water purifier, lake water detection and other TDS detection.

### Parameter

Table 1

Item	Parameter
insulation resistance	$\geq 50M\Omega$ (not exposed)
measurement range	0-2000ppm
measurement accuracy	$\pm 5\%$ F.S.
Operating temperature	$\leq 70^{\circ}C$
Operating voltage	$\leq 5.0V$
Product Specifications	quick connect-2
Cable length	58cm




Figure 2: Sensor Structure

**Instructions**

1. Connect the TDS probe to the TDS sensor module.
2. Power on the TDS sensor module and put the TDS probe into the solution to be tested for testing.
3. After the test is completed, rinse the sensor electrode end with a small amount of pure or deionized water.
4. Dry the cleaned sensor and install a protective cover on the electrode end.

**Cable connection****Table 2**

Cable color	Definition
Blue (central core)	+
Cable (shielded network cable)	-

**Precautions**

- ◆ The sensor electrode end must be cleaned before use.
- ◆ TDS probe should not be placed too close to the edge of the container, otherwise it will affect the reading.
- ◆ The TDS probe head and wire are waterproof and can be immersed in water, but the connection interface and signal adapter board are not waterproof, so pay attention to waterproofing when using.
- ◆ After the test is completed, be sure to wipe off the residual water on the probe, otherwise it will affect the test accuracy in the next test.
- ◆ The electrode head should be kept clean during long-term storage, and the sensor should be put back in the box and stored at room temperature.

**Zhengzhou Winsen Electronics Technology Co., Ltd**

Addr.: NO.299 Jin Suo Road, National Hi-Tech Zone,  
Zhengzhou, 450001 China

Tel.: 86-371-67169097 Fax: +86- 371-60932988

E-mail: [sales@winsensor.com](mailto:sales@winsensor.com)

Website: [www.winsen-sensor.com](http://www.winsen-sensor.com)